



Connectors, Snap-Fit, F-Style, Recessed, Electric Ivory

By Hubbell Wiring Device-Kellems
Catalog # [SFGRFEI](#)

Connectors, Snap-Fit, F-Style, Recessed, Electric Ivory



Application

Snap-Fit Gold F-Connector, Recessed

General

Contact	Beryllium Copper
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	iSTATION RCA and F-Keystone Connectors
Material - Mounting Hardware Style	Snap-On- Snap-Fit Gold, Recessed
Temperature Rating	Per TIA
Type	F-Type
UPC	662620202396

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Connectivity	Female to Female
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalog Page - Wiring AA-10 Catalog Page](#)
[Catalog Page - Wiring_Catalog_Z6_CatPage](#)
[Catalogs - Wiring Full Catalog](#)
[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs: 4, 6, 8 and 10 inch](#)
[Literature - Connexion 2.0 Zone Distribution System](#)
[Warranty - Industrial & Commercial Products](#)

Related Products

[SFGRFBK - Snap-Fit, Recessed F-Coax Connector, Black](#)
[SFGRFGY - Connectors, Snap-Fit, F-Style, Recessed, Gray](#)
[SFFEX - Snap-Fit, F-Coax Connector, Electric Ivory](#)
[NSF70I - Net Select, Snap-Fit, With F Connector, Ivory](#)
[SFF3GEI - F Coax, Snap-Fit, 3GHz, Gold, Electric Ivory](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-SFGRFEI-SPEC-EN | REV 5/2023