



## INFINE Connector, Audio/Video Connector, RCA Gold Pass-thru, F/F Coupler, Gray/Blue

By Hubbell Wiring Device-Kellems  
Catalog # [SFRCBFFGY](#)



INFINE Connector, Audio/Video Connector, RCA Gold Pass-thru, F/F Coupler, Gray/Blue

### Features

- High quality Gold plating
- Seamless Hubbell system integration
- Deliver composite, component or digital signals

### Application

Snap-Fit RCA Jack

### General

Contact	Beryllium Copper
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	iSTATION RCA and Data Keystone Connectors
Material - Mounting Hardware	Snap-On- Snap-Fit
Style	Blue Insulator
Temperature Rating	Per TIA
Type	RCA, Pass-Thru, F to F Coupler
UPC	662620850566

### Dimensions

Display Size	Standard Sized Product
--------------	------------------------

### Electrical Ratings

Connectivity	Plug-N-Play
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

### Logistics

Carton Quantity	25
-----------------	----

### Product Assets

[Catalog Page - Wiring AA-10 Catalog Page](#)  
[Catalog Page - Wiring Z-7 Catalog page](#)  
[Catalogs - Wiring Full Catalog](#)  
[Warranty - Industrial & Commercial Products](#)

### Related Products

[SFRCBFFOW - INFINE Connector, Audio/Video Connector, RCA Gold Pass-thru, F/F Coupler, Office White/Blue](#)  
[SFRCBFFBK - INFINE Connector, Audio/Video Connector, RCA Gold Pass-thru, F/F Coupler, Black/Blue](#)  
[SFRCBFFEI - INFINE Connector, Audio/Video Connector, RCA Gold Pass-thru, F/F Coupler, Electric Ivory/Blue](#)  
[SFRCBFFW - INFINE Connector, Audio/Video Connector, RCA Gold Pass-thru, F/F Coupler, White/Blue](#)  
[SFRCORFFGY - RCA Connector, Female to Female, Orange Insulator, Gray Housing](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-SFRCBFFGY-SPEC-EN | REV 5/2023