




Wiring Device-Kellems

RCA Connector, Female to Female, Orange Insulator, Gray Housing

By Hubbell Wiring Device-Kellems
Catalog # [SFRCORFFGY](#)



RCA Connector, Female to Female, Orange Insulator, Gray Housing

Application

Snap-Fit RCA Jack

General

Contact	Beryllium Copper
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	iSTATION RCA and Data Keystone Connectors
Material - Mounting Hardware	Snap-On- Snap-Fit
Style	Orange Insulator
Temperature Rating	Per TIA
Type	RCA, Pass-Thru, F to F Coupler
UPC	662620286310

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Connectivity	Plug-N-Play
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalog Page - Wiring Z-7 Catalog page](#)
[Catalogs - Wiring Full Catalog](#)
[Warranty - Industrial & Commercial Products](#)

Related Products

[SFRCGNFFGY - INFINE Connector, Audio/Video Connector, RCA Gold Pass-thru, F/F Coupler, Gray/Green](#)
[SFRCBFFGY - INFINE Connector, Audio/Video Connector, RCA Gold Pass-thru, F/F Coupler, Gray/Blue](#)
[SFRCORFFEI - RCA Connector, Female to Female, Orange Insulator, Electric Ivory Housing](#)
[SFRCYFFGY - Snap-Fit, Audio/Video Connector, RCA Gold Pass-thru, F/FCoupler, Yellow/Gray](#)
[SFRCORFFW - RCA Connector, Female to Female, Orange Insulator, White Housing](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-SFRCORFFGY-SPEC-EN | REV 5/2023