



RCA Connector, Female to Female, Red Insulator, Gray Housing

By Hubbell Wiring Device-Kellems
Catalog # [SFRCRFFGY](#)



RCA Connector, Female to Female, Red Insulator, Gray Housing

Features

- High quality Gold plating
- Seamless Hubbell system integration
- Deliver composite, component or digital signals

General

Color	Gray
Contact	Beryllium Copper
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	iSTATION RCA and Data Keystone Connectors
Material - Mounting Hardware	Snap-On- Snap-Fit
Series	Accessory
Style	RCA Gold Pass-through F/F Coupler Red Insulator
Temperature Rating	Per TIA
Type	Snap-Fit Connector
UPC	662620849225

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Connectivity	Plug-N-Play
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalog Page - Wiring T-46 Catalog page](#)
[Catalog Page - Wiring AA-10 Catalog Page](#)
[Catalog Page - Wiring Z-7 Catalog page](#)
[Catalogs - Wiring Full Catalog](#)
[Warranty - Industrial & Commercial Products](#)

Related Products

[SFRCRFFBK - RCA Connector, Female to Female, Red Insulator, Black Housing](#)
[SFRCRFFEI - Snap-Fit, Audio/Video Connector, RCA Gold Pass-thru, F /F Coupler, Red/Electric Ivory](#)
[SFRCBKFFGY - RCA Connector, Female to Female, Black Insulator, Gray Housing](#)
[SFRCBFFGY - INFIne Connector, Audio/Video Connector, RCA Gold Pass-thru, F/F Coupler, Gray/Blue](#)
[SFRCRFFW - Snap-Fit, Audio/Video Connector, RCA Gold Pass-thru, F/F Coupler, Red/White](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-SFRCRFFGY-SPEC-EN | REV 5/2023