



## Keystone USB Jack, Snap-Fit, V3.0, A to A, Black

By Hubbell Wiring Device-Kellems  
Catalog # [SFUSBAA3BK](#)



Keystone USB Jack, Snap-Fit, V3.0, A to A, Black

### General

Contact	Copper
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Snap-Fit Data and AV Connectors
Material - Mounting Hardware	Snap-On- Snap-Fit
Style	USB
Temperature Rating	Per TIA
Type	Data
UPC	662620326122

### Dimensions

Display Size	1-Unit
--------------	--------

### Electrical Ratings

Connectivity	Female to Female
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

### Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

### Logistics

Carton Quantity	25
-----------------	----

### Product Assets

[Catalog Page - Wiring Z-5 Catalog page](#)  
[Catalogs - Wiring Full Catalog](#)  
[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs: 4, 6, 8 and 10 inch](#)  
[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)  
[Warranty - Industrial & Commercial Products](#)

### Related Products

[SF5ECOY - Inline Coupler, Snap-Fit, Slim, X Over 10/100, Gray](#)  
[SFUSBABB - Snap-Fit, Keystone, USB, A to B, Black](#)  
[SFSC6 - Snap-Fit, Inline Coupler, Slim, Cat6, Shielded](#)  
[SFC5EBK - Snap-Fit, Inline Coupler, Cat5e, Slim, Black](#)  
[SFUSBABW - Snap-Fit, Keystone, USB, A to B, White](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-SFUSBAA3BK-SPEC-EN | REV 5/2023