

Switches and Lighting Controls,  
Industrial/Commercial Grade,  
SNAPConnect Series, Toggle  
Switches, Three Way, 15A 120/277V  
AC Toggle

By Hubbell Wiring Device-Kellems  
Catalog # [SNAP1203LA](#)

Switches and Lighting Controls, Industrial/Commercial Grade,  
SNAPConnect Series, Toggle Switches, Three Way, 15A 120/277V  
AC, Light Almond Toggle

Features

- Steel, zinc plated bridge is corrosion resistant
- Thread cleaning captive mounting screw
- Automatic self-grounding staple assures continuity to wall box

Application

General Purpose

Performance

- Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute
- Electrical - Max. Continuous Current - 15A
- Electrical - Max. Working Voltage - 277V AC
- Electrical - Overload - Minimum 4.8 times rated current for 100 cycles
- Electrical - Temperature Rise - 30°C maximum at rated current
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact
- Mechanical - Terminal Accommodations - Uses SNAPConnect Connector

General

Action	SPDT
Catalog Number	SNAP1203LA
Color	Light Almond
EU RoHS Indicator	No
Item Type	Three Way Toggle Switch
Material	Thermoplastic
Number Of Poles	Single Pole
Operating Temperature	Maximum continuous 75°C and without Impact minimum -40 °C
Series	SnapConnect Devices



Specifications

	• Base Material - Thermoplastic, Black
	• Contacts - Silver Alloy
	• Terminals - Brass
	• Toggle Material - Thermoplastic
	• Top Material - Thermoplastic, Blue
Style	Three Way
Type	Toggle
UPC	783585313962

Dimensions

Dimensions	4.18 in x 1.3 in x 1.74 in
Height	1.74 in
Length	4.18 in
Width	1.3 in

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC
Voltage Rating Description	120-277 VAC

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK D-8 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - SNAP1203LANA AutoCAD Drawing](#)

[Installation Manuals - WIRING\\_PD2403\\_INSTALLINST](#)  
[Literature - SNAPConnect® Devices](#)  
[Sales Drawings - WDK\\_SNAP1203\\_DRAWING\\_PDF](#)

[Warranty - Industrial & Commercial Products](#)  
[Video - SNAPConnect Devices](#)



**A Hubbell brand**

©2025 Hubbell Incorporated. All rights reserved  
WDK-SNAP1203LA-SPEC-EN | REV 3/2025