

Straight Blade Devices,  
Receptacles, Style Line Decorator  
Duplex, SNAPConnect, Half  
Controlled, 15A 125V, 2-Pole 3-Wire  
Grounding, Nylon, Blue

By Hubbell Wiring Device-Kellems  
Catalog # [SNAP2152C1BL](#)

Straight Blade Devices, Receptacles, Style Line Decorator  
Duplex, SNAPConnect, Half Controlled, 15A 125V, 2-Pole 3-Wire  
Grounding, Nylon, Blue

Features

- Audible SNAP, indicates solid connection
- Reduces installation time
- Split Circuit, Half Controlled
- Power symbol is clearly visible

Application

SNAPConnect Permanently Marked

Performance

- Electrical: Current Interrupting- Certified for current interrupting at full rated current
- Electrical: Dielectric Voltage- Withstands 2,000V minimum
- Mechanical: Product Identification Ratings are a permanent part of the device
- Environmental: Flammability- UL 94V-2
- Environmental: Operating Temperature- Maximum continuous 75°C
- minimum -40°C (w/o impact)

General

Catalog Number	SNAP2152C1BL
Color	Blue
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Style Line Decorator
Material	Nylon
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Permanently Marked Receptacles
Style	Style Line Decorator
Type	One Controlled Face, Split Circuit



Dimensions

Dimensions	3.28 in x 1.64 in x 1.1 in
Display Size	Standard Sized Product
Height	1.1 in
Length	3.28 in
Weight	0.2 lb
Width	1.64 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Connectorized
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding
Wire Size	#12 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA, C22.2, No. 42 File 285</li><li>• Fed. Spec. W-C-596</li><li>• NEMA® WD-6 Compliant</li><li>• UL Listed to UL498 File No. E2186, ASHRAE Energy Efficiency Standard 90.1 2010</li><li>• California Title 24 2013</li></ul>
Nema Rating	5-15R

Product Assets



**A Hubbell brand**