

HUBBELL
Wiring Device-Kellems

**Straight Blade Devices,
Receptacles, Style Line Decorator
Duplex, SNAPConnect, Controlled,
15A 125V, 2-Pole 3-Wire Grounding,
Nylon, Red**

By Hubbell Wiring Device-Kellems
Catalog # [SNAP2152C2R](#)

Straight Blade Devices, Receptacles, Style Line Decorator
Duplex, SNAPConnect, Controlled, 15A 125V, 2-Pole 3-Wire
Grounding, Nylon, Red



Features

- Audible SNAP, indicates solid connection
- Reduces installation time
- Split Circuit, Fully Controlled
- Power symbol is clearly visible

General

Application	SNAPConnect Permanently Marked
Catalog Number	SNAP2152C2R
Color	Red
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Style Line Decorator
Material	Nylon
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical: Current Interrupting-Certified for current interrupting at full rated current Electrical: Dielectric Voltage-Withstands 2,000V minimum Mechanical: Product Identification Ratings are a permanent part of the device Environmental: Flammability-UL 94V-2 Environmental: Operating Temperature- Maximum continuous 75°C minimum -40°C (w/o impact)
Series	Permanently Marked Receptacles
Style Type	Style Line Decorator Two Controlled Faces

Dimensions

Dimensions	3.28 in x 1.64 in x 1.1 in
Display Size	Standard Sized Product
Height	1.1 in
Length	3.28 in
Weight	0.2 lb
Width	1.64 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Connectorized
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding
Wire Size	#12 AWG

Certifications And Compliance

Industry Standard(s)	Certified to CSA, C22.2, No. 42 File 285 Fed. Spec. W-C-596 NEMA® WD-6 Compliant UL Listed to UL498 File No. E2186, ASHRAE Energy Efficiency Standard 90.1 2010 California Title 24 2013
Nema Rating	5-15R

Product Assets

- [Catalog Page - WDK A-23 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Automatic Receptacle Control Product Guide](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK-SNAP2152C2R-SPEC-EN | REV 6/2024