

Straight Blade Devices,
Receptacles, Style Line Decorator
Duplex, SNAPConnect, Half
Controlled, 20A 125V, 2-Pole 3-Wire
Grounding, Blue

By Hubbell Wiring Device-Kellems
Catalog # [SNAP2162C1BL](#)



Straight Blade Devices, Receptacles, Style Line Decorator
Duplex, SNAPConnect, Half Controlled, 20A 125V, 2-Pole 3-Wire
Grounding, Blue

Features

- Permanent power symbol remains clearly visible after installation
- Audible SNAP, indicates solid connection
- Self-grounding clip

Application

SNAPConnect Permanently Marked

Performance

- Electrical: Current Interrupting- Certified for current interrupting at full rated current
- Electrical: Dielectric Voltage- Withstands 2,000V minimum
- Mechanical: Product Identification Ratings are a permanent part of the device
- Environmental: Flammability- UL 94V-2
- Environmental: Operating Temperature- Maximum continuous 75°C
- minimum -40°C (w/o impact)

General

Catalog Number	SNAP2162C1BL
Color	Blue
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Item Type	Style Line Decorator
Material	Nylon
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Permanently Marked Receptacles
Style	Style Line Decorator
Type	One Controlled Face, Split Circuit

Dimensions

Dimensions	3.28 in x 1.64 in x 1.1 in
Display Size	Standard Sized Product
Height	1.1 in
Length	3.28 in
Weight	0.2 lb
Width	1.64 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Connectorized
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding
Wire Size	#12 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA, C22.2, No. 42 File 285• Fed. Spec. W-C-596• NEMA® WD-6 Compliant• UL Listed to UL498 File No. E2186, ASHRAE Energy Efficiency Standard 90.1 2010• California Title 24 2013
Nema Rating	5-20R

Product Assets



A Hubbell brand