



Straight Blade Devices, Receptacles, Style Line Decorator Duplex, SNAPConnect, 20A 125V, 2-Pole 3-Wire Grounding, Nylon, Red

By Hubbell Wiring Device-Kellems
Catalog # [SNAP2162C1R](#)



Straight Blade Devices, Receptacles, Style Line Decorator Duplex, SNAPConnect, 20A 125V, 2-Pole 3-Wire Grounding, Nylon, Red

Features

- Audible SNAP, indicates solid connection
- Reduces installation time
- Split Circuit, Half Controlled
- Power symbol is clearly visible

Application

SNAPConnect Permanently Marked

General

Color	Red
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Item Type	Style Line Decorator
Material	Nylon
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Maximum continuous 75°C and minimum -40°C without impact
Performance	<ul style="list-style-type: none"> • Electrical: Current Interrupting- Certified for current interrupting at full rated current • Electrical: Dielectric Voltage- Withstands 2,000V minimum • Mechanical: Product Identification Ratings are a permanent part of the device • Environmental: Flammability- UL 94V-2 • Environmental: Operating Temperature- Maximum continuous 75°C • minimum -40°C (w/o impact)
Series	Permanently Marked

Dimensions

Dimensions	3.28 in x 1.64 in x 1.1 in
Display Size	Standard Sized Product
Height	1.1 in
Length	3.28 in
Weight	0.2 lb
Width	1.64 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Connectorized
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Conductors	3-Wire Grounding
Number Of Wires	3-Wire
Wire Size	#12 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA, C22.2, No. 42 File 285 • Fed. Spec. W-C-596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186, ASHRAE Energy Efficiency Standard 90.1 2010 • California Title 24 2013
----------------------	--

Nema Rating	5-20R
-------------	-------

Product Assets

[Catalog Page - Wiring A-18 Catalog page](#)
[Catalogs - Wiring Full Catalog](#)
[Literature - Automatic Receptacle Control Product Guide](#)

Style
Type

Permanently Marked
Receptacles
Style Line Decorator
One Controlled Face, Split
Circuit



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-SNAP2162C1R-SPEC-EN | REV 5/2023