

Straight Blade Devices,
Receptacles, SNAP-CONNECT
Connector, SNAP-CONNECT Series,
2-Pole 3-Wire Grounding, 20A 125V,
Stranded, Right Angled

By Hubbell Wiring Device-Kellems
Catalog # [SNAP2RNAX](#)



Straight Blade Devices, Receptacles, SNAP-CONNECT
Connector, SNAP-CONNECT Series, 2-Pole 3-Wire Grounding,
20A 125V, Stranded, Right Angled, Clear terminal with 6-inch
leads, USA

Features

- Transparent housing to inspect contacts
- Audible SNAP, indicates solid connection
- Reduces installation time
- Fully insulated design

Application

Quick Connection

Performance

- Electrical: Current Interrupting- Certified for current interrupting at full rated current
- Electrical: Dielectric Voltage- Withstands 2,000V minimum
- Mechanical: Product Identification Ratings are a permanent part of the device
- Environmental: Flammability- UL 94V-2
- Environmental: Operating Temperature- Maximum continuous 75°C
- minimum -40°C (w/o impact)

General

Catalog Number	SNAP2RNAX
Color	Clear
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	SNAPConnect Connector
Material	Polycarbonate
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none">• Contact - Brass• Terminal Body - PBT

Type
UPC

- Wire - #12 AWG, T90 Nylon FT-1, PVC 90°C (min)
- Pigtailed Connector
783585251974

Dimensions

Dimensions	1.48 in x 0.78 in x 0.63 in
Display Size	Standard
Height	0.63 in
Length	1.48 in
Weight	0.05 lb
Width	0.78 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Connectorized
Current / Amperage Rating	15 A - 20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Conductor Range	Pre-Wired #12 THHN
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding
Wire Size	#12 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA, C22.2, No. 42 File 285• Fed. Spec. W-C-596• NEMA® WD-6 Compliant• UL Listed to UL498 File No. E2186
----------------------	----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Nema Rating	Non-NEMA
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	20
Pallet Quantity	10000

Product Assets

[Catalog Page - WDK Q-5 Catalog Page](#)
[Catalog Page - WDK L-5 Catalog Page](#)
[Catalog Page - WDK X-14 Catalog Page](#)

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - SNAP2RNA AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2489_INSTALLINST](#)
[Literature - Duct Products Guide](#)
[Literature - Healthcare Product Solutions](#)
[Literature - Electrical Products - Healthcare Solutions](#)
[Literature - SNAPConnect® Devices](#)
[Literature - Emergency Preparedness for Healthcare](#)
[Sales Drawings - WDK_SNAP2RNA_DRAWING_PDF](#)
[Specifications - WDK-SNAP2RNAX-SPEC-EN](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Autoguard GFCI Receptacles](#)
[Video - SNAPConnect Devices](#)

