

SNAPConnect® Heavy Duty  
Commercial AUTOGUARD® Self-  
Test GFCI Receptacle, 15A, Ivory

By Hubbell Wiring Device-Kellems  
Catalog # [SNAPGF15I](#)



Straight Blade Devices, SNAP-Connect, AUTOGUARD®, Self-Test, GFCI Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Ivory

Features

- Audible SNAP, indicates solid connection
- Patented AUTOGUARD® self test technology
- Triple wipe construction
- Patented AUTOGUARD® Self-Test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

Application

Commercial Grade

General

Catalog Number	SNAPGF15I
Color	Ivory
Item Type	Style Line GFCI Receptacle
Material	Nylon
Series	Heavy Duty
Size	4.12 in x 1.75 in x 1.48 in
Specifications	<ul style="list-style-type: none"><li>• Base - Nylon</li><li>• Face - Nylon</li><li>• Contacts - Brass</li><li>• Mounting Screws - Stainless Steel</li><li>• Mounting Strap - Galvanized Steel</li><li>• Power Contacts - Brass</li></ul>
Type	Standard
UPC	783585746357

Dimensions

Dimensions	1.48 in x 1.75 in x 4.12 in
Height	4.12 in
Length	1.48 in
Width	1.75 in

Electrical Ratings

Current / Amperage Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	1875 W

Conductor Related

Wire Size	SNAPConnect
-----------	-------------

Certifications And Compliance

Industry Standard(s)	UL 943 and Meets All NEC® Requirements
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK K-5 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - M14625\\_ACAD](#)  
[Sales Drawings - M14625](#)  
[Specifications - SNAPGF15I](#)  
[Warranty - Industrial & Commercial Products](#)