

SNAPConnect® Heavy Duty Commercial AUTOGUARD® Self- Test GFCI Receptacle, 20A, Gray

By Hubbell Wiring Device-Kellems

Catalog # [SNAPGF20GRY](#)

Straight Blade Devices, SNAP-Connect, AUTOGUARD®, Self-Test, GFCI Receptacle, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Gray



Features

- Audible SNAP, indicates solid connection
- Patented AUTOGUARD® self test technology
- Triple wipe construction
- Patented AUTOGUARD® Self-Test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

General

Application	Commercial Grade
Catalog Number	SNAPGF20GRY
Color	Gray
Item Type	Style Line GFCI Receptacle
Material	Nylon
Series	Heavy Duty
Size	4.12 in x 1.75 in x 1.48 in
Type	Standard
UPC	783585746401

Dimensions

Dimensions	1.48 in x 1.75 in x 4.12 in
Height	4.12 in
Length	1.48 in
Width	1.75 in

Electrical Ratings

Current / Amperage Rating	20 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	2500 W

Conductor Related

Wire Size	SNAPConnect
-----------	-------------

Certifications And Compliance

Industry Standard(s)	UL 943 and Meets All NEC® Requirements
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK K-5 Catalog Page](#)

[Catalogs - WDK Catalog Full 2024](#)

[Engineering Drawing - M14625_ACAD](#)

[Sales Drawings - M14625](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK-SNAPGF20GRY-SPEC-EN | REV 6/2024