

# SNAPConnect® Heavy Duty Hospital Grade AUTOGUARD® Self- Test GFCI Receptacle, 20A, Light Almond

By Hubbell Wiring Device-Kellems  
Catalog # [SNAPGF83LA](#)

SNAPConnect® Straight Blade GFCI Receptacle, Commercial Hospital Grade, Self-Test, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R.



## Features

- Audible SNAP, indicates solid connection
- Patented AUTOGUARD® self test technology
- Triple wipe construction
- Patented AUTOGUARD® Self-Test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

## General

Application	Commercial Hospital Grade
Catalog Number	SNAPGF83LA
Color	Light Almond
Item Type	Self test GFCI receptacle
Material	Nylon
Series	Hospital Grade
Size	4.12 in x 1.75 in x 1.48 in
Type	Standard
	Standard
UPC	783585746531

## Dimensions

Dimensions	1.48 in x 1.75 in x 4.12 in
Height	4.12 in
Length	1.48 in
Width	1.75 in

## Electrical Ratings

Current / Amperage Rating	20 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	2500 W

## Conductor Related

Wire Size	SNAPConnect
-----------	-------------

## Certifications And Compliance

Industry Standard(s)	UL 943 and Meets All NEC® Requirements
Nema Rating	5-20R

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - WDK A-17 Catalog Page](#)  
[Catalog Page - WDK L-15 Catalog Page](#)  
[Catalog Page - WDK L-5 Catalog Page](#)  
[Catalog Page - WDK K-6 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - M14625\\_ACAD](#)  
[Installation Manuals - PD2986](#)  
[Sales Drawings - M14625](#)  
[Warranty - Industrial & Commercial Products](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
WDK-SNAPGF83LA-SPEC-EN | REV 6/2024