

SNAPConnect® Heavy Duty Hospital Grade AUTOGUARD® Self- Test GFCI Receptacle, 20A, Red

By Hubbell Wiring Device-Kellems

Catalog # [SNAPGF83R](#)

SNAPConnect® Straight Blade GFCI Receptacle, Commercial Hospital Grade, Self-Test, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R.



Features

- Audible SNAP, indicates solid connection
- Patented AUTOGUARD® self test technology
- Triple wipe construction
- Patented AUTOGUARD® Self-Test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

General

Application	Commercial Hospital Grade
Catalog Number	SNAPGF83R
Color	Red
Item Type	Self test GFCI receptacle
Material	Nylon
Series	Hospital Grade
Size	4.12 in x 1.75 in x 1.48 in
Type	Standard
	Standard
UPC	783585746548

Dimensions

Dimensions	1.48 in x 1.75 in x 4.12 in
Height	4.12 in
Length	1.48 in
Width	1.75 in

Electrical Ratings

Current / Amperage Rating	20 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	2500 W

Conductor Related

Wire Size	SNAPConnect
-----------	-------------

Certifications And Compliance

Industry Standard(s)	UL 943 and Meets All NEC® Requirements
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK A-17](#) [Catalog Page - WDK L-15](#) [Catalog Page - WDK L-5](#) [Catalog Page - WDK K-6](#) [Catalog Page - WDK Catalog Full 2024](#)
[Engineering Drawing - M14625_ACAD](#)
[Installation Manuals - PD2986](#)
[Literature - Hospital Grade GFCI Receptacles](#)
[Sales Drawings - M14625](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK-SNAPGF83R-SPEC-EN | REV 6/2024