

# SNAPConnect® Heavy Duty Commercial Tamper- Resistant/Weather Resistant AUTOGUARD® Self-Test GFCI Receptacle, 15A, White

By Hubbell Wiring Device-Kellems  
Catalog # [SNAPGFTW15W](#)



Straight Blade Devices, SNAP-Connect, Weather and Tamper-Resistant, AUTOGUARD®, Self-Test, GFCI Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, White

## Features

- Audible SNAP, indicates solid connection
- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (406.12) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® Self-Test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

## General

Application	Commercial Grade
Catalog Number	SNAPGFTW15W
Color	White
Environmental Conditions	Weather Resistant
Item Type	Style Line GFCI Receptacle
Material	Nylon
Series	Heavy Duty
Size	4.12 in x 1.75 in x 1.48 in
Type	Tamper-Resistant, Weather Resistant
UPC	783585746142

## Dimensions

Dimensions	1.48 in x 1.75 in x 4.12 in
Height	4.12 in
Length	1.48 in
Width	1.75 in

## Electrical Ratings

Current / Amperage Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	1875 W

## Conductor Related

Wire Size	SNAPConnect
-----------	-------------

## Certifications And Compliance

Industry Standard(s)	UL 943 and Meets All NEC® Requirements
Nema Rating	5-15R

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - WDK K-7 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - M14625\\_ACAD](#)  
[Sales Drawings - M14625](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK-SNAPGFTW15W-SPEC-EN | REV 6/2024