

SNAPConnect® Heavy Duty Hospital Grade Tamper- Resistant/Weather Resistant AUTOGUARD® Self-Test GFCI Receptacle, 15A, Gray

By Hubbell Wiring Device-Kellems
Catalog # [SNAPGFTW82GRY](#)



Straight Blade SNAPConnect® Receptacle, GFCI, Tamper and Weather Resistant, Commercial Hospital Grade, Self-Test, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R.

Features

- Audible SNAP, indicates solid connection
- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (406.12) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® Self-Test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

Application

- Commercial Hospital Grade

General

Catalog Number	SNAPGFTW82GRY
Color	<ul style="list-style-type: none">• Gray
Environmental Conditions	Weather Resistant
Item Type	Self test GFCI receptacle
Material	Nylon
Series	Hospital Grade
Size	4.12 in x 1.75 in x 1.48 in
Type	<ul style="list-style-type: none">• Tamper-Resistant, Weather Resistant• Tamper-Resistant, Weather Resistant
UPC	783585746227

Dimensions

Dimensions	1.48 in x 1.75 in x 4.12 in
Height	4.12 in
Length	1.48 in
Width	1.75 in

Electrical Ratings

Current / Amperage Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	1875 W

Conductor Related

Wire Size	SNAPConnect
-----------	-------------

Certifications And Compliance

Industry Standard(s)	UL 943 and Meets All NEC® Requirements
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK A-17](#) [Catalog Page - WDK K-7](#) [Catalog Page - WDK Catalog Full 2024](#)
[Engineering Drawing - M14625_ACAD](#)
[Installation Manuals - PD2986](#)
[Sales Drawings - M14625](#)
[Warranty - Industrial & Commercial Products](#)

