

SNAPConnect® Heavy Duty Hospital Grade Tamper- Resistant/Weather Resistant AUTOGUARD® Self-Test GFCI Receptacle, 20A, Black

By Hubbell Wiring Device-Kellems
Catalog # [SNAPGFTW83BLK](#)



Straight Blade SNAPConnect® Receptacle, GFCI, Tamper and Weather Resistant, Commercial Hospital Grade, Self-Test, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R.

Features

- Audible SNAP, indicates solid connection
- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (406.12) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® Self-Test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

General

Application	Commercial Hospital Grade
Catalog Number	SNAPGFTW83BLK
Color	Black
Environmental Conditions	Weather Resistant
Item Type	Self test GFCI receptacle
Material	Nylon
Series	Hospital Grade
Size	4.12 in x 1.75 in x 1.48 in
Type	Tamper-Resistant, Weather Resistant
	Tamper-Resistant, Weather Resistant
UPC	783585746272

Dimensions

Dimensions	1.48 in x 1.75 in x 4.12 in
Height	4.12 in
Length	1.48 in
Width	1.75 in

Electrical Ratings

Current / Amperage Rating	20 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	2500 W

Conductor Related

Wire Size	SNAPConnect
-----------	-------------

Certifications And Compliance

Industry Standard(s)	UL 943 and Meets All NEC® Requirements
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK A-17](#) [Catalog Page - WDK K-7](#) [Catalog Page - WDK L-5](#) [Catalog Page - WDK L-14](#) [Catalog Page Catalogs - WDK Catalog Full 2024](#) [Engineering Drawing - M14625_ACAD](#) [Installation Manuals - PD2986](#) [Sales Drawings - M14625](#) [Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK-SNAPGFTW83BLK-SPEC-EN | REV 6/2024