

# SNAPConnect® Heavy Duty Hospital Grade Tamper- Resistant/Weather Resistant AUTOGUARD® Self-Test GFCI Receptacle, 20A, Gray

By Hubbell Wiring Device-Kellems  
Catalog # [SNAPGFTW83GRY](#)



Straight Blade SNAPConnect® Receptacle, GFCI, Tamper and Weather Resistant, Commercial Hospital Grade, Self-Test, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R.

## Features

- Audible SNAP, indicates solid connection
- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (406.12) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® Self-Test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

## General

|                          |                                     |
|--------------------------|-------------------------------------|
| Application              | Commercial Hospital Grade           |
| Catalog Number           | SNAPGFTW83GRY                       |
| Color                    | Gray                                |
| Environmental Conditions | Weather Resistant                   |
| Item Type                | Self test GFCI receptacle           |
| Material                 | Nylon                               |
| Series                   | Hospital Grade                      |
| Size                     | 4.12 in x 1.75 in x 1.48 in         |
| Type                     | Tamper-Resistant, Weather Resistant |
|                          | Tamper-Resistant, Weather Resistant |
| UPC                      | 783585746296                        |

## Dimensions

|            |                             |
|------------|-----------------------------|
| Dimensions | 1.48 in x 1.75 in x 4.12 in |
| Height     | 4.12 in                     |
| Length     | 1.48 in                     |
| Width      | 1.75 in                     |

## Electrical Ratings

|                           |              |
|---------------------------|--------------|
| Current / Amperage Rating | 20 A         |
| Phase                     | Single Phase |
| Voltage Rating            | 125 VAC      |
| Wattage                   | 2500 W       |

## Conductor Related

|           |             |
|-----------|-------------|
| Wire Size | SNAPConnect |
|-----------|-------------|

## Certifications And Compliance

|                      |  |
|----------------------|--|
| Industry Standard(s) | UL 943 and Meets All NEC® Requirements |
| Nema Rating          | 5-20R                                  |

## Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

## Product Assets

[Catalog Page - WDK A-17](#) [Catalog Page - WDK K-7](#) [Catalog Page - WDK L-5](#) [Catalog Page - WDK L-14](#) [Catalog Page Catalogs - WDK Catalog Full 2024](#) [Engineering Drawing - M14625\\_ACAD](#) [Installation Manuals - PD2986](#) [Sales Drawings - M14625](#) [Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK-SNAPGFTW83GRY-SPEC-EN | REV 6/2024