

# SNAPConnect® Heavy Duty Hospital Grade Tamper- Resistant/Weather Resistant AUTOGUARD® Self-Test GFCI Receptacle, 20A, White

By Hubbell Wiring Device-Kellems  
Catalog # [SNAPGFTW83W](#)



Straight Blade SNAPConnect® Receptacle, GFCI, Tamper and Weather Resistant, Commercial Hospital Grade, Self-Test, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R.

## Features

- Audible SNAP, indicates solid connection
- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (406.12) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® Self-Test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

## General

Application	Commercial Hospital Grade
Catalog Number	SNAPGFTW83W
Color	White
Environmental Conditions	Weather Resistant
Item Type	Self test GFCI receptacle
Material	Nylon
Series	Hospital Grade
Size	4.12 in x 1.75 in x 1.48 in
Type	Tamper-Resistant, Weather Resistant
	Tamper-Resistant, Weather Resistant
UPC	783585746333

## Dimensions

Dimensions	1.48 in x 1.75 in x 4.12 in
Height	4.12 in
Length	1.48 in
Width	1.75 in

## Electrical Ratings

Current / Amperage Rating	20 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	2500 W

## Conductor Related

Wire Size	SNAPConnect
-----------	-------------

## Certifications And Compliance

Industry Standard(s)	UL 943 and Meets All NEC® Requirements
Nema Rating	5-20R

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - WDK A-17](#) [Catalog Page - WDK K-7](#) [Catalog Page - WDK L-5](#) [Catalog Page - WDK L-14](#) [Catalog Page - WDK X-15](#) [Catalog Page Catalogs - WDK Catalog Full 2024](#) [Engineering Drawing - M14625\\_ACAD](#) [Installation Manuals - PD2986](#) [Literature - Healthcare Product Solutions](#) [Literature - Hospital Grade GFCI Receptacles](#) [Sales Drawings - M14625](#) [Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK-SNAPGFTW83W-SPEC-EN | REV 6/2024