

Straight Blade Devices, Receptacles,
Single, Commercial Grade, 2-Pole 3-
Wire Grounding, 15A 125V, 5-15R,
Orange, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [SR15IG](#)

Straight Blade Devices, Receptacles, Single, Commercial Grade, 2-Pole
3-Wire Grounding, 15A 125V, 5-15R, Orange, Single Pack

Features

- Receptacles
- Single
- Commercial Grade
- 2-Pole 3-Wire Grounding

Application

Select-Spec Devices

General

Catalog Number	SR15IG
Color	Orange
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585328898

Dimensions

Display Size	Standard Sized Product
--------------	------------------------



Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	1875

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - SR15IG](#)
[Warranty - Industrial & Commercial Products](#)

