



Wiring Device-Kellems

# USB Charger Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, 1) 5A "C" USB and "A" Ports, Gray

By Hubbell Wiring Device-Kellems  
Catalog # [USB15AC5GY](#)



USB Charger Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, 1) 5A "C" USB and "A" Ports, Gray

## Features

- High Power 5 Amp, 5 Volt USB Output
- Combination Ports, One Type A, One Type C
- Tamper Resistant Commercial Grade Duplex Compatible
- USB Ports Rated 10,000 Cycles

## General

Color	Gray
Number Of Poles	2-Pole
Series	Heavy Duty
Style	Style Line Decorator
Type	One Type A, One Type-C Port
UPC	883778307195

## Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating Description	125 V

## Conductor Related

Number Of Wires	3-Wire
-----------------	--------

## Certifications and Compliance

Nema Rating	5-15R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2023](#)  
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WDK-USB15AC5GY-SPEC-EN | REV 1/2024