



Copper Solutions, Patch Cord, AV, 8- Pin, Plenum, 15' Length, Black

By Hubbell Wiring Device-Kellems
Catalog # [VGA6P15BK](#)



Copper Solutions, Patch Cord, AV, 8- Pin, Plenum, 15' Length, Black

Application

Horizontal Cable W/Male Ends

General

Boot Type	None
EU RoHS Indicator	Yes
Item Type	X-END AV Plug-n-Play System
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	VGA
Temperature Rating	Per TIA
Type	VGA, Plug-n-Play
UPC	662620286921

Dimensions

Outside Diameter	0.375
------------------	-------

Electrical Ratings

Voltage Rating	600V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#28 AWG

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Warranty - Industrial & Commercial Products](#)

Related Products

- [VGA6P35BK - Patch Cord, AV, 8-Pin, Plenum, Black, 35'](#)
- [VGA6P100BK - Patch Cord, AV, 8-Pin, Plenum, Black, 100'](#)
- [VGA6P50BK - Patch Cord, AV, 8-Pin, Plenum, Black, 50'](#)
- [VGA6P75BK - Patch Cord, AV, 8-Pin, Plenum, Black, 75'](#)
- [VGA6P25BK - Patch Cord, AV, 8-Pin, Plenum, Black, 25'](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-VGA6P15BK-SPEC-EN | REV 5/2023