



Switches and Lighting Control, Occupancy Sensor Switch, Decorator, 8A 120/277V AC, White

By Hubbell Wiring Device-Kellems
Catalog # [WLS1278W](#)

Switches and Lighting Control, Occupancy Sensor Switch,
Decorator, 8A 120/277V AC, White



Application

Compatible with most LED and CFL

General

Color	White
Performance	<ul style="list-style-type: none"> • Electrical - Indication - Green indicator light • Electrical - Operating voltage - 120/277V, 50/60Hz • Environment - Operating Environment - Indoor use only • Environment - Operating temperature - 32°F to 104°F (0°C to 40°C) • Environment - Range - RF range is 30 ft (10m) obstructed, 60 ft (18m) line of sight • Environment - Relative humidity - 0% to 90% humidity, non-condensing • Mechanical - Capacity - Up to 9 WLAS accessory switches can be configured to work together with one WLS1278 • Mechanical - Wire Size - #20 to 16 AWG (0.5 to 1.5mm²) solid or stranded wire
Series	Passive Infrared
Style	Accessories
Type	<ul style="list-style-type: none"> • Wireless - Ceiling Mount • Wireless - Wall Mount
UPC	783585159485

Electrical Ratings

Amperage Rating	8 A
Current / Amperage Rating	8 A
Current Rating	8 A
Voltage Rating	120-277 VAC
Voltage Rating Description	120/277V AC

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	24
-----------------	----

Product Assets

- [Catalog Page - Wiring E-17 Catalog Page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Installation Manuals - WIRING_PD2513_PD2514_INSTALLINST](#)
- [Literature - Sensors Troubleshooting Guide](#)
- [Literature - Load Control Application Guide](#)
- [Literature - Healthcare Application Guide](#)
- [Literature - WL-Series Wireless Controls Application Guide](#)
- [Sales Drawings - WDK_WLS1278_DRAWING_PDF](#)
- [Warranty - HMOSS Occupancy Motion Sensors](#)





A proud member of the Hubbell Family.