

Wire Management, Hose Containment Grips, Split Fitting, 24" Mesh Length, Cable Dia:0.75 in-1.25 in



By Hubbell Wiring Device-Kellems
Catalog # [014021113](#)

Wire Management, Hose Containment Grips, Split Fitting, 24"
Mesh Length, Cable Dia:0.75 in-1.25 in

Features

- These grips will prevent serious injury to personnel and damage to equipment by holding the hose in place in the event of hose failure
- Kellems® patented Hose Containment Grips are made of stainless steel double weave mesh construction for high strength and come complete with hose clamps
- Split fitting to fit AN-818 nuts
- Fitting is positioned over nut and located with internal flange

General

Application	Used on high pressure, flexible hose lines to prevent the hose from whipping violently in the event of hose failure at the fitting
Approx Breaking Strength	6,000 lbs
Catalog Number	014021113
Item Type	Split Fitting (Type F)
Material	Stainless Steel
Series	Split Fitting
UPC	783585300443

Conductor Related

Cable Diameter Range	0.75 in-1.25 in
----------------------	-----------------

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[Catalog Page - WDK W-46 Catalog Page](#)
[Catalog Page - WDK W-47 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Literature - Wire Management Solutions Brochure](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Kellems Wire Management Solutions](#)
[Video - Kellems Wire Management Solutions](#)



A Hubbell brand