




Wiring Device-Kellems

Wire Management, Hose Containment Grips, Split Fitting, 24" Mesh Length, Cable Dia:0.38 in-0.69 in

By Hubbell Wiring Device-Kellems
Catalog Number [014021208](#)



Wire Management, Hose Containment Grips, Split Fitting, 24" Mesh Length, Cable Dia:0.38 in-0.69 in.

Features

- These grips will prevent serious injury to personnel and damage to equipment by holding the hose in place in the event of hose failure
- Kellems® patented Hose Containment Grips are made of stainless steel double weave mesh construction for high strength and come complete with hose clamps
- Split fitting to fit AN-818 nuts
- Fitting is positioned over nut and located with internal flange

Application

Used on high pressure, flexible hose lines to prevent the hose from whipping violently in the event of hose failure at the fitting

General

Approx Breaking Strength	2,900 lbs
Item Type	Split Fitting (Type F)
Material	Stainless Steel
UPC	783585300535

Conductor Related

Cable Diameter Range	0.38 in-0.69 in
----------------------	-----------------

Product Assets

- [Catalog Page - Wiring X-47 Catalog page](#)
- [Literature - WIRING_WLFVM034](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Literature - Pulp & Paper Solutions](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Kellems Wire Management Solutions](#)
- [Video - Kellems Wire Management Solutions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK_CA-014021208-SPEC-EN | REV 5/2023