



Support Grips, Offset Eye, Single Weave, Closed Mesh, Tin-Coated Bronze, 0.75-0.99"

By Hubbell Wiring Device-Kellems
Catalog # [02201039](#)

Kellems® Standard Support Grip, Offset Eye, Single Weave, Closed Mesh, Tin-Coated Bronze, 0.75-0.99".



Features

- Offset eye
- Strand equalizers position wires for equal loading throughout grip length
- Eye assemblies provide eye reinforcement at support hardware

Application

Offset Eye

General

Approx Breaking Strength	950 lbs
Color	<ul style="list-style-type: none">• Metallic• Métallique
Construction	Woven
Material	Bronze, Tin Coated
Material - Mounting Hardware	Screw Hook or Beam Clamp
Performance	<ul style="list-style-type: none">• Mechanical - Approximate Breaking Strength - 950 (4,226)• Mechanical - Working Load - 95 (422.6) Lbs. (N)
Series	Standard Duty
Style	Closed Mesh, Single Weave
Type	<ul style="list-style-type: none">• Offset Eye• Offset Eye
UPC	783585301310

Conductor Related

Cable Diameter Range	0.75 in-0.99 in
Cable Size	.75"-.99" (1.90-2.51)

Certifications and Compliance

Industry Standard(s)	CSA Certified
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalog Page - WDK W-22 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Installation Manuals - WIRING_PD2004_INSTALLINST](#)
- [Literature - WIRING_WLFVM034](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Literature - Wiring_WLFVM032](#)
- [Literature - Wiring_WLBVM044](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK_02201039_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Kellems Wire Management Solutions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-02201039-SPEC-EN | REV 1/2024