

Support Grips, Double Eye, Single Weave, Split Mesh, Rod Closing, Tin-Coated Bronze, 0.75-0.99"

By Hubbell Wiring Device-Kellems
Catalog # 02203003

Support Grips, Double Eye, Single Weave, Split Mesh, Rod Closing, Tin-Coated Bronze, 0.75-0.99"

Features

- Double eye
- Strand equalizers position wires for equal loading throughout grip length
- Eye assemblies provide eye reinforcement at support hardware

Performance

- Mechanical - Approximate Breaking Strength - 1,020 (4,537)
- Mechanical - Working Load - 102 (453.7) Lbs. (N)

General

Approx Breaking Strength	1,020 lbs
Catalog Number	02203003
Color	Metallic
Construction	Woven
EU RoHS Indicator	Yes
Material	Bronze, Tin Coated
Material - Mounting Hardware	Screw Hook or Beam Clamp
Series	Standard Duty
Specifications	<ul style="list-style-type: none">• Equalizer - Bronze• Eye - Copper• Rod - Stainless Steel• Strand - Tin-coated bronze• Tag - Mylar
Style	Split Mesh, Rod Closing
UPC	783585302942



Conductor Related

Cable Diameter Range	0.75 in-0.99 in
Cable Size	.75"-.99" (1.90-2.51)

Certifications And Compliance

Industry Standard(s)	CSA Certified
----------------------	---------------

Logistics

Carton Quantity	150
-----------------	-----

Product Assets

- Catalog Page - [WDK W-21 Catalog Page](#)
- Catalogs - [WDK Catalog Full 2024](#)
- Installation Manuals - [WIRING_PD2004_INSTALLINST](#)
- Literature - [Wire Management Solutions Brochure](#)
- Literature - [FOOD & BEVERAGE SOLUTIONS](#)
- Literature - [PULP & PAPER SOLUTIONS](#)
- Literature - [Pulp & Paper Solutions](#)
- Literature - [FOOD & BEVERAGE SOLUTIONS](#)
- Sales Drawings - [WDK_02203003_DRAWING_PDF](#)
- Specifications - [Wiring 02203003 Specification Sheet](#)
- Specifications - [2203003 Specification Sheet French](#)
- Specifications - [02203003 Specification Sheet](#)
- Warranty - [Industrial & Commercial Products](#)
- Video - [Kellems Wire Management Solutions](#)
- Video - [Kellems Wire Management Solutions](#)