

Universal Eye, Support Grip, 1.5-1.7",
Stainless Steel, Closed Mesh

By Hubbell Wiring Device-Kellems
Catalog # [02401055](#)

Support Grips, Universal Eye, Single Weave, Closed Mesh,
Stainless Steel, 1.50-1.74"

Features

- Universal eye
- Strand equalizers position wires for equal loading throughout grip length
- Eye assemblies provide eye reinforcement at support hardware

Application

Universal Eye

Performance

- Mechanical - Approximate Breaking Strength - 4,490 (19,972)
- Mechanical - Working Load - 449 (1997.2) Lbs. (N)

General

Approx Breaking Strength	4,490 lbs
Catalog Number	02401055
Color	Stainless Steel
Construction	Woven
EU RoHS Indicator	Yes
Material	Stainless Steel
Material - Mounting Hardware	Screw Hook or Beam Clamp
Series	Standard Duty
Specifications	<ul style="list-style-type: none">• Equalizer - Stainless Steel• Link - Bronze• Lug - Bronze• Strand - Stainless Steel• Tag - Mylar
Style	Closed Mesh, Single Weave



Type	Universal Eye
UPC	783585309446

Conductor Related

Cable Diameter Range	1.5 in-1.74 in
Cable Size	1.50"-1.74" (3.81-4.42)

Certifications And Compliance

Industry Standard(s)	CSA Certified
----------------------	---------------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK W-23 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_PD2004_INSTALLINST](#)
[Literature - Wire Management Solutions Brochure](#)
[Literature - FOOD & BEVERAGE SOLUTIONS](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - FOOD & BEVERAGE SOLUTIONS](#)
[Sales Drawings - WDK_02401055_DRAWING_PDF](#)
[Specifications - 02401055 Specification Sheet](#)
[Specifications - Wiring 02401055 Specification Sheet](#)
[Specifications - 2401055 Specification Sheet French](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Kellems Wire Management Solutions](#)
[Video - Kellems Wire Management Solutions](#)