



Kellems Wire Management, Dusttight Grips, Strain Relief, .73-.97", 1", Non-Insulated

By Hubbell Wiring Device-Kellems
Catalog # [073031204](#)



Dusttight Strain Relief Non Insulated Grips, 1" NPT, 0.73-0.97"
(1.85-2.46 cm).

Features

- Aluminum fitting
- Galvanized steel mesh for high strength

Application

Light Duty

General

Color	<ul style="list-style-type: none"> • Metallic • Métallique
Construction	Woven
Item Type	Dust-Tight Strain Relief Grips
Material	Aluminum Fittings, Galvanized Steel Mesh
Material - Mounting Hardware	Locknut or Tapped Hole
Performance	<ul style="list-style-type: none"> • Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2 (Fitting) • Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
Series	Dust-Tight
Style	For Insulated Cables
Thread Size	1" NPT
Type	<ul style="list-style-type: none"> • Non-Insulated, Wide Range • Non-Insulated, Wide Range
UPC	783585330044

Dimensions

Display Size	1" NPT
Trade Size	1

Conductor Related

Cable Diameter Range	0.73 in-0.97 in
Cable Size	.73"- .97" (1.85-2.46)

Certifications and Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK W-55 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Installation Manuals - WIRING_30920060_INSTALLINST](#)
- [Literature - WIRING_WLFVM034](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Literature - Wiring_WLFVM032](#)
- [Literature - Wiring_WLBVM044](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK_073031204_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Kellems Wire Management Solutions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-073031204-SPEC-EN | REV 1/2024