



Kellems Wire Management, I-Grips, .56-.73", Galvanized

By Hubbell Wiring Device-Kellems
Catalog # [07310003](#)

Plastic Coated Galvanized Steel Mesh Strain Relief I-Grips for Insulated Cables, 0.56-0.73" (1.42-1.85 cm).



Features

- Controls cable arc-of-bend
- Provides heavy-duty strain relief
- Easily attached to Insulgrip plug and connector body

Application

Light Duty

General

Approx Breaking Strength	200 lbs
Color	<ul style="list-style-type: none">• Metallic• Métallique
Construction	Woven
Item Type	I-Grips
Material	Galvanized Steel Mesh for Insulated Cables, Plastic Coated
Material - Mounting Hardware	Mounts on Cord Grip
Series	For Plug & Connectors
Style	I-Grips, For Hubbell Devices
Type	<ul style="list-style-type: none">• Eyelets (2)• Eyelets (2)
UPC	783585332161

Dimensions

Display Size	Standard Sized
--------------	----------------

Conductor Related

Cable Diameter Range	0.56 in-0.73 in
Cable Size	.56"-.73" (1.42-1.85)
Cable Specification	Mesh Length @ Nom. Dia. : 6" (15.24 cm)

Certifications and Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	20
-----------------	----

Product Assets

[Catalog Page - WDK W-56 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Installation Manuals - WIRING_30920075_INSTALLINST](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Wire Management Solutions Brochure](#)
[Literature - Wiring_WLFVM032](#)
[Literature - Wiring_WLBVM044](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_07310003_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Kellems Wire Management Solutions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-07310003-SPEC-EN | REV 1/2024