



# Switches and Lighting Controls, Hubbell- PRO Series, Toggle Switches, General Purpose AC, Single Pole, 15A 120/277V AC, Back and Side Wired

By Hubbell Wiring Device-Kellems  
Catalog # [1201LA](#)



Hubbell-PRO Single Pole Toggle Switch, General Purpose AC,  
15A 120/277V AC, Back and Side Wired.

## Features

- Steel, zinc plated bridge is corrosion resistant
- Color Coded by Amperage makes inspection easy even when installed
- Strip gauge for accurate wiring

## Application

Back and Side Wired

## General

Color	• Light Almond
Number Of Poles	Single Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute</li> <li>• Electrical - Max. Continuous Current - 15A</li> <li>• Electrical - Max. Working Voltage - 277V AC</li> <li>• Electrical - Overload - Minimum 4.8 times rated current for 100 cycles</li> <li>• Electrical - Temperature Rise - 30°C maximum at rated current</li> <li>• Environmental - Flammability - UL 94V-2</li> <li>• Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact</li> <li>• Mechanical - Terminal Accommodations - #14 AWG min. - #10 AWG max. solid and stranded copper wire only</li> </ul>

Series

Heavy Duty

## Dimensions

Dimensions	4.18 in x 1.49 in x 1.83 in
Height	1.83 in
Length	4.18 in
Weight	0.15 lb
Width	1.49 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC
Voltage Rating Description	120-277 VAC

## Conductor Related

Wire Size	#14 AWG to #10 AWG
-----------	--------------------

## Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog Page - WDK D-6 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - 1201LA AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD1242\\_INSTALLINST](#)
- [Sales Drawings - WDK\\_1201\\_DRAWING\\_PDF](#)
- [Warranty - Industrial & Commercial Products](#)

Style  
Type

Single Pole  
• Toggle  
• Toggle  
UPC  
783585181318



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-1201LA-SPEC-EN | REV 1/2024