



Straight Blade Devices, Tamper Resistant Decorator Duplex Receptacle, Hospital Grade, Hubbell-Pro, 15A 125V, 2- Pole 3-Wire Grounding, 5-15R, White

By Hubbell Wiring Device-Kellems
Catalog # [2172WTRA](#)

Straight Blade Devices, Tamper Resistant Decorator Duplex Receptacle, Hospital Grade, Hubbell-Pro, 15A 125V, 2- Pole 3-Wire Grounding, 5-15R, White.



General

Color	
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	0.5
Item Type	Style Line Decorator Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none">Electrical - Current Interrupting - Certified for current interrupting at full rated currentElectrical - Dielectric Voltage - Withstands 2,000V minimumEnvironmental - Flammability - UL 94V-2Environmental - Operating Temperature - Maximum continuous 75°C, minimum -40°C (w/o impact)Mechanical - Product Identification - Ratings are a permanent part of the deviceMechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor onlyMechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Series	Hubbell-Pro
Style	Style Line decorator
Type	
UPC	783585541891

Dimensions

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">Certified to CSA, C22.2, No. 42 File 285Fed. Spec. W-C-596NEMA® WD-6 CompliantUL Listed to UL498 File No. E2186
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK L-9 Catalog Page](#)
[Catalog Page - WDK A-27 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_PD2504_INSTALLINST](#)
[Literature - Tamper-Resistant Receptacles for Healthcare](#)
[Literature - Heavy Duty Tamper-Resistant Receptacles](#)
[Literature - Duct Products Guide](#)
[Literature - Tamper-Resistant Receptacles](#)
[Literature - Hubbell-Pro Hospital Grade Receptacles](#)
[Literature - Hubbell-PRO Hospital Grade TR Receptacles](#)
[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)
[Warranty - Industrial & Commercial Products](#)

Dimensions	3.28 in x 1.57 in x 1.15 in
Height	1.15 in
Length	3.28 in
Weight	0.2 lb
Width	1.57 in

[Video - Tamper-Resistant Receptacles](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-2172WTRA-SPEC-EN | REV 5/2024