

Straight Blade Devices,
Receptacles, Duplex,
Commercial/Industrial Grade, 2-
Pole 3-Wire Grounding, 20A 125V,
5-20R, Light Almond

By Hubbell Wiring Device-Kellems
Catalog # [5352LA](#)



Straight Blade Devices, Receptacles, Duplex,
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A
125V, 5-20R, Light Almond

Features

- Slender/compact design
- Smooth face
- Triple wipe contacts

Application

Hubbell-Pro Extra Heavy Duty

General

Catalog Number	5352LA
Color	Light Almond
Environmental Conditions	Indoor Dry unless protected by additional means
Material	Thermoplastic/Composite
Mounting Type	Screw Mount
Number Of Poles	2-Pole
Series	Hubbell-PRO
Size	Standard Sized Product
Style	Smooth Face
Temperature Rating	Maximum continuous 75°C; minimum -40°C (w/o impact)
Type	Standard Duplex
UPC	783585530833

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A

Phase	Single Phase
Voltage Rating	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	UL File No. E2186, Certified to CSA 22.2, No. 42 File 285, Fed. Spec. W-C-596, NEMA® WD-6 Compliant
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK A-28 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - M14187_ACAD](#)
- [Installation Manuals - WIRING_PD1579_INSTALLINST](#)
- [Sales Drawings - M14187](#)
- [Specifications - WIRING_5352LA_spec](#)
- [Specifications - 5352LA Specification Sheet French](#)
- [Specifications - 5352LA Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)