

5362AL

By Hubbell Wiring Device-Kellems  
Catalog # [5362AL](#)

Straight Blade Devices, Receptacles, Duplex,  
Commercial/Industrial Grade, 20A 125V, 2-Pole 3-Wire  
Grounding, 5-20R, Almond, Single Pack.

Application

Hubbell-Pro Heavy Duty

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminal wire leads identified in accordance with UL 498

General

Catalog Number	5362AL
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Hubbell-PRO
Specifications	<ul style="list-style-type: none"><li>• Automatic Self-grounding</li><li>• Staple - Stainless steel</li><li>• Base - PBT</li><li>• Contacts - Brass</li><li>• Face - Nylon</li><li>• Mounting Screws - Zinc plated steel</li><li>• Mounting Strap - Galvanized steel</li></ul>
Style	Finder Groove Face
Type	Standard Duplex
UPC	783585109831



Dimensions

Dimensions	3.28 in x 1.41 in x 1.09 in
Display Size	Standard Sized Product
Height	1.09 in
Length	3.28 in
Weight	0.15 lb
Width	1.41 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA 22.2, No. 42</li><li>• Fed. Spec. W-C-596</li><li>• NEMA® WD-6 Compliant</li><li>• UL Listed to UL498 File No. E2186</li></ul>
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Sales Drawings - WDK\\_5362AL\\_DRAWING\\_PDF](#)
- [Specifications - Wiring 5362AL Specification Sheet](#)
- [Specifications - 5362AL Specification Sheet](#)
- [Specifications - 5362AL Specification Sheet French](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
WDK\_CA-5362AL-SPEC-EN | REV 4/2025