

EdgeConnect™, Hubbell-Pro
Receptacle, 20A 125V, 5-20R,
Screwless Terminal, Gray

By Hubbell Wiring Device-Kellems
Catalog # [5362STGY](#)



Straight Blade Devices, EdgeConnect™, Hubbell-Pro Receptacle,
Industrial Grade, 2-Pole 3-Wire, 20A 125V, 5-20R, Screwless
Terminal, Gray

Features

- Back wired screwless termination for faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Triple and Double Wipe Contacts
- Easy access split circuit tab

Application

Hubbell-PRO

General

Catalog Number	5362STGY
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Receptacle
Material	Thermoplastic/C
Mounting Type	Screw Mount
Number Of Poles	2-Pole
Series	EdgeConnect™
Size	Standard Sized Product
Style	Finder Groove Face
Temperature Rating	Maximum continuous 75°C; minimum -40°C (w/o impact)
Type	Standard Duplex
UPC	783585727592

Electrical Ratings

Current / Amperage Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single
Voltage Rating	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	• UL Listed to UL498 File No. E2186 • Certified to CSA 22.2, No. 42 File 285 • Fed. Spec. W-C-596,NEMA® WD-6 Compliant
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[3D Product View - WDK_DuplexReceptacles](#)
[Brochures - EdgeConnect Brochure French](#)
[Brochures - EdgeConnect Brochure](#)
[Catalog Page - WDK A-21 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - PD3029](#)
[Literature - EdgeConnect™ Technology FAQ](#)
[Literature - EdgeConnect™ Technology](#)
[Literature - EdgeConnect™ Termination vs Standard Push Wire](#)
[Sales Drawings - M14621](#)
[Specifications - 5362STGY Specification Sheet French](#)
[Specifications - WIRING_5362STGY_spec](#)
[Specifications - 5362STGY Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)