

Straight Blade Devices, Duplex
Receptacle, Hospital Grade,
Hubbell-Pro, 15A 125V, 2-Pole 3-
Wire Grounding, 5-15R, Red

By Hubbell Wiring Device-Kellems
Catalog # 8200RED



Straight Blade Devices, Duplex Receptacle, Hospital Grade,
Hubbell-Pro, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Red.

Features

- Triple wipe contacts
- High impact resistant face with circuit I.D. marking area
- Steel mounting strap

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	8200RED
EU RoHS Indicator	No
Horsepower - Maximum	0.5
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Hubbell-Pro
Specifications	<ul style="list-style-type: none">• Automatic Self-grounding Staple - Stainless steel• Base - PBT• Clamping Plate - Plated steel• Face - Nylon• Ground Contacts - Brass• Mounting Screws - Zinc plated steel

Style	• Mounting Strap - Galvanized steel
UPC	• Power Contacts - Brass
	Smooth Face
	783585197487

Dimensions

Dimensions	3.28 in x 1.57 in x 1.15 in
Display Size	Standard Sized Product
Height	1.15 in
Length	3.28 in
Weight	0.15 lb
Width	1.57 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA, C22.2, No. 42 File 285• Fed. Spec. W-C-596• NEMA® WD-6 Compliant• UL Listed to UL498 File No. E2186
Nema Rating	5-15R

Logistics

Carton Quantity	10	Literature - Hubbell-Pro Hospital Grade Receptacles
		Literature - Duct Products Guide
		Sales Drawings - WDK_8200_DRAWINGS_PDF
		Specifications - Wiring 8200RED Specification Sheet
		Specifications - 8200RED Specification Sheet
		Specifications - 8200RED Specification Sheet French
		Warranty - Industrial & Commercial Products

Product Assets

- Catalog Page - WDK A-27 Catalog Page
- Catalog Page - WDK L-8 Catalog Page
- Catalogs - WDK Catalog Full 2024
- Engineering Drawing - 8200RED AutoCAD Drawing

