

Switches and Lighting Controls,
Dimmer, Rotary Dimmer, Single
Pole, 1000W, Beige

By Hubbell Wiring Device-Kellems
Catalog # [AR101](#)

Switches and Lighting Controls, Dimmer, Rotary Dimmer, Single
Pole, 1000W, Beige

Features

- Rotary Dimmer
- Single Pole
- 1000W

Performance

Environmental - Operating Temperatures - Max Continuous
-75°C, Minimum- -40°C Without Impact

General

Catalog Number	AR101
EU RoHS Indicator	No
Item Type	Rotary Control Dimmer
Number Of Poles	Single Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Architectural Grade
Specifications	• Dimmer Style - Architectural Grade Rotary • Product Type - Dimmers • Switch Type - Single Pole
Style	Single Pole
Type	Rotary Control



UPC783585224213

Dimensions

Weight0.65 lb

Electrical Ratings

Voltage Rating	120 VAC
Voltage Rating Description	120 VAC
Wattage	1000 W

Certifications And Compliance

Industry Standard(s)UL Listed

Logistics

Carton Quantity10

Product Assets

[Catalog Page - WDK D-21 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Specifications - Wiring AR101 Specification Sheet](#)
[Specifications - AR101 Specification Sheet](#)
[Specifications - AR101 Specification Sheet French](#)
[Warranty - Industrial & Commercial Products](#)