

2-Gang, Rectangular, Cast Iron Box,
Deep, Fully Adjustable, Aluminum
Top

By Hubbell Wiring Device-Kellems
Catalog # [BA4233](#)



Flush Concrete Floor Box Series, 2-Gang, Rectangular, Cast Iron
Box, Deep, Fully Adjustable, Aluminum Top

Features

- Corrosion resistant for on-grade applications
- Leveling feet provide before pour adjustability
- Oversized threaded conduit access holes for low voltage

General

Application - For Use On	Concrete
Catalog Number	BA4233
Construction	Case Iron
EU RoHS Indicator	No
Finish Type	Aluminum
Knockouts	6) 3/4"
Material	Cast Iron
Mounting Method	Cast Into Concrete
Number of Gang(s)	2-Gang
Series	Flush Rectangular - B24 Series
Size	3-Gang
Specifications	• Capacity Per Gang - 36.5 cu. in. (598.1 cm3) • Collar Material - Aluminum • Min. Depth of Pour - 3.75" (95.3)
UPC	783585106304

Dimensions

Dimensions	4.84 in x 8.06 in x 3.38 in
Height	3.38 in
Length	4.84 in
Width	8.06 in

Conductor Related

Cable Entry	From Top
-------------	----------

Certifications And Compliance

Industry Standard(s)	• UL/CSA • UL514
----------------------	--

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - BA4233 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1437_INSTALLINST](#)
[Sales Drawings - WDK_BA4233_DRAWING_PDF](#)
[Specifications - BA4233 Specification Sheet French](#)
[Specifications - BA4233 Specification Sheet](#)
[Specifications - Wiring BA4233 Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)