

Kellems Wire Management, Deluxe  
Cord Grips, Straight Male Non-  
Metallic, .500-.625", 3/4" with Mesh

By Hubbell Wiring Device-Kellems  
Catalog # [CG610NM](#)

Kellems Wire Management, Deluxe Cord Grips, Straight Male  
Non-Metallic, .500-.625", 3/4" with Mesh

Features

- Nylon Fitting
- Non-metallic mesh is corrosion resistant
- Neoprene bushing is oil and watertight

Application

Straight Male- Form 3

Performance

- Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2(Fitting)
- Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
- Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)
- Environmental - Wet Locations - Suitable for use in wet locations when used with a listed sealing ring between box and fitting

General

Catalog Number	CG610NM
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.
Item Type	Deluxe Cord Grips
Material	Nylon Fittings, Non-Metallic Mesh
Material - Mounting Hardware Series	Locknut or Tapped Opening Deluxe Cord Grips
Specifications	<ul style="list-style-type: none"><li>• Bushings - Neoprene</li><li>• Fittings - Nylon</li><li>• NPT Thread Size - 3/4 Inch</li><li>• Strand - Non-metal</li></ul>
Style	For Insulated Cables



Temperature Rating	Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)
Thread Size	3/4" NPT
Type	Straight Male Thread
UPC	783585335063

Dimensions

Display Size	3/4" NPT
--------------	----------

Conductor Related

Cable Diameter Range	0.500 in-0.625 in
Cable Size	.500"-.625" (1.27-1.59)
Conductor Range	0.5-0.625 in (1.27-1.59 mm)
Number of Conductors	Single

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalog Page - WDK W-52](#)
- [Catalog Page - WDK W-53](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Literature - FOOD & BEVERAGE SOLUTIONS](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - FOOD & BEVERAGE SOLUTIONS](#)
- [Specifications - CG610NM Specification Sheet](#)
- [Specifications - Wiring CG610NM Specification Sheet](#)
- [Specifications - CG610NM Specification Sheet French](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Kellems Wire Management Solutions](#)
- [Video - Kellems Wire Management Solutions](#)