

Straight Blade Devices, Duplex  
Receptacle, Commercial Grade,  
Smooth Face, 20A 125V, 2-Pole 3-  
Wire Grounding, 5-20R, Side Wired  
Only, Red

By Hubbell Wiring Device-Kellems  
Catalog # [CR20R](#)



Straight Blade Devices, Duplex Receptacle, Commercial Grade,  
Smooth Face, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Side  
Wired Only, Red

Features

- Easy access split circuit tab
- Fork terminal capable
- Smooth face
- Triple wipe contacts

General

Catalog Number	CR20R
Color	Red
EU RoHS Indicator	No
Item Type	Traditional Duplex
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
UPC	783585197555

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A

Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	2500

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
Pallet Quantity	9000

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - M10319\\_ACAD](#)
- [Sales Drawings - M10319](#)
- [Specifications - CR20R Specification Sheet English](#)
- [Specifications - CR20R Specification Sheet French](#)
- [Specifications - WIRING\\_CR20R\\_spec](#)
- [Warranty - Industrial & Commercial Products](#)