

Straight Blade Devices, Tamper
Resistant Duplex Receptacle,
Commercial Grade, Smooth Face,
20A 125V, 2-Pole 3- Wire
Grounding, 5-20R, Side Wired Only

By Hubbell Wiring Device-Kellems
Catalog # [CR20RTR](#)



Straight Blade Devices, Tamper Resistant Duplex Receptacle,
Commercial Grade, Smooth Face, 20A 125V, 2-Pole 3- Wire
Grounding, 5-20R, Side Wired Only, Red

Features

- Tamper-resistant shutter complies with national electrical code requirements
- Smooth face
- Triple wipe contacts

Application

Commercial Specification Grade

General

Catalog Number	CR20RTR
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
UPC	783585197616

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	20 A
-----------------	------

Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	2500

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
Pallet Quantity	8000

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - M10514_ACAD](#)
- [Sales Drawings - M10514](#)
- [Specifications - CR20RTR Specification Sheet French](#)
- [Specifications - CR20RTR Specification Sheet English](#)
- [Specifications - WIRING_CR20RTR_spec](#)
- [Warranty - Industrial & Commercial Products](#)