

Locking Devices, Twist-Lock®,
Industrial, Receptacle, 50A, 250V,
2-Pole 3-Wire Grounding, Non-
NEMA, Screw Terminal, Black

By Hubbell Wiring Device-Kellems
Catalog # [CS8269](#)



Locking Devices, Twist-Lock®, Industrial, Receptacle, 50A, 250V,
2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V0
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #10 AWG - #6 AWG solid or stranded copper wire only

General

Catalog Number	CS8269
Color	Black
EU RoHS Indicator	No
Item Type	Receptacles
Material	Phenolic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	- Body - Phenolic - Contacts - Brass - Face - Phenolic - Insulator - Phenolic - Terminal Screws - Steel
UPC	783585828909

Dimensions

Dimensions	2.69 in x 2.12 in x 2.36 in
Display Size	Standard Sized Product
Height	2.36 in
Length	2.69 in
Weight	0.7 lb
Width	2.12 in

Electrical Ratings

Amperage Rating	50 A
Connectivity	Screw Terminals

Current / Amperage Rating	50 A
Current Rating	50 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#10 AWG to #6 AWG

Certifications And Compliance

Industry Standard(s)	- Certified to CSA C22.2 No.42 - Listed to UL 498
----------------------	---

Logistics

Carton Quantity	10
Pallet Quantity	1600

Product Assets

- [Catalog Page - WDK B-56](#)
- [Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - WIRING_PD1344_PD1346_F1357_INSTALLINST](#)
- [Literature - Food Processing Guide](#)
- [Literature - 50 Amp Twist-Lock® Devices](#)
- [Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)
- [Literature - Emergency Preparedness for Healthcare](#)
- [Sales Drawings - WDK_CS8269_DRAWING_PDF](#)
- [Specifications - CS8269 Specification Sheet](#)
- [Specifications - CS8269 Specification Sheet French](#)
- [Specifications - Wiring CS8269 Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Insulgrip Twist-Lock and Straight Blade Devices](#)
- [Video - Insulgrip Twist-Lock and Straight Blade Devices](#)
- [Video - Twist-Lock Devices](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK_CA-CS8269-SPEC-EN | REV 4/2025