

Heavy Duty Products, IEC Pin and Sleeve Devices, Marine Grade, Cable Set, 100A 120/208V AC, 3-Pole 4-Wire No Neutral, Pre-wired Male End Only, Yellow

Par Hubbell Wiring Device-Kellems
No de catalogue [CW100IT5](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Marine Grade, Ship to Shore, Cable Set, 100A 120/208V AC, 3- Pole 4-Wire No Neutral, Pre-wired Male End Only, Yellow, For Boats with.

Caractéristiques

- Factory assembled
- Rugged, watertight and corrosion resistant
- 100% inspection to ensure quality performance
- Assemblage en usine
- Robuste, étanche et résistant à la corrosion
- Inspection à 100% pour garantir la qualité des performances

Performance

Environnement - Résistance à l'humidité - Aptitude IP56

Général

Numéro de catalogue	CW100IT5
Couleur	
Indicateur RoHS de l'UE	Non
Conditions environnementales	
Type d'article	Extrémités mâle et femelle moulées, pour utilisation avec les transformateurs d'isolation et les treuils de câble
Veste	STOW
Matériau	Cuivre
CUP	783585503004

Caractéristiques électriques

Intensité nominale	100 A
Courant / Intensité nominale	100 A
Valeur nominale actuelle	100 A
Phase	Triphasé
Tension Rating	120/208V AC kV
Puissance	20800

Chef d'orchestre

Longueur du cordon	1200
--------------------	------

Certifications et conformité

Norme(s) industrielle(s)	Répertorié UL
--------------------------	---------------

Documentation

- [Catalogues - WDK Catalog Full 2024](#)
- [Dessins de vente - WDK_CW100IT5_DRAWING_PDF](#)
- [Garantie - Industrial & Commercial Products](#)
- [Littérature - Hubbell Marine Full Line Catalog](#)
- [Manuels d'installation - WIRING_PD1426_INSTALLINST](#)
- [Page du catalogue - WDK AA-5 Catalog Page](#)
- [Page du catalogue - WDK AA-19 Catalog Page](#)
- [Spécifications - CW100IT5](#)
- [Spécifications - WIRING_CW100IT5_spec](#)
- [Vidéo - Marine Electrical Products](#)