

Heavy Duty Products, IEC Pin and Sleeve Devices, Marine Grade, Cable Set, 100A 125/250V, 2-Pole 3-Wire No Neutral, Pre-Wired Male End Only

Par Hubbell Wiring Device-Kellems
No de catalogue [CW125IT4](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Marine Grade, Ship to Shore, Cable Set, 100A 125/250V, 2-Pole 3-Wire No Neutral, Pre-wired Male End Only, Yellow, For Boats with Cable.

Caractéristiques

- Factory assembled
- Rugged, watertight and corrosion resistant
- 100% inspection to ensure quality performance
- Assemblage en usine
- Robuste, étanche et résistant à la corrosion
- Inspection à 100% pour garantir la qualité des performances

Performance

Environnement - Résistance à l'humidité - Aptitude IP56

Général

Numéro de catalogue	CW125IT4
Couleur	
Indicateur RoHS de l'UE	Non
Conditions environnementales	
Type d'article	Extrémités mâle et femelle moulées, pour utilisation avec les transformateurs d'isolation et les treuils de câble
Veste	STOW
Matériau	Cuivre
CUP	783585502908

Caractéristiques électriques

Intensité nominale	100 A
Courant / Intensité nominale	100 A
Valeur nominale actuelle	100 A
Phase	Monophasé
Tension Rating	125/250 VAC
Puissance	25000

Chef d'orchestre

Longueur du cordon	1500
--------------------	------

Certifications et conformité

Norme(s) industrielle(s)	Répertorié UL
--------------------------	---------------

Documentation

- [Catalogues - WDK Catalog Full 2024](#)
- [Dessins de vente - WDK_CW125IT4_DRAWING_PDF](#)
- [Garantie - Industrial & Commercial Products](#)
- [Littérature - Hubbell Marine Full Line Catalog](#)
- [Manuels d'installation - WIRING_PD1426_INSTALLINST](#)
- [Page du catalogue - WDK AA-5 Catalog Page](#)
- [Page du catalogue - WDK AA-19 Catalog Page](#)
- [Spécifications - WIRING_CW125IT4_spec](#)
- [Spécifications - CW125IT4](#)
- [Vidéo - Marine Electrical Products](#)

