



Straight Blade Devices, Receptacles, Duplex, Decorator/Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Brown, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [DR15](#)



Straight Blade Duplex Receptacle,
Decorator/Commercial/Industrial Grade, 2-Pole 3-Wire
Grounding, 15A 125V, 5-15R.

Features

- Aesthetic Style Line® decorator design
- Smooth face
- Triple wipe contacts

Application

Commercial Specification Grade

General

Color	<ul style="list-style-type: none"> • Brown • Marron
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Decorator Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94 V-2 • Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal

Dimensions

Dimensions	1.29 in x 1.06 in x 3.28 in
Display Size	Standard Sized Product
Height	3.28 in
Length	1.29 in
Weight	0.2 lb
Width	1.06 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA, C22.2, No. 42 • Fed. Spec. W-C-596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
Nema Rating	5-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

Accommodation - #14-#10
AWG copper stranded or
solid conductor only

- Mechanical - Terminal
Identification - Terminals
identified in accordance
with UL 498 and CSA

[Catalog Page - WDK AA-43 Catalog Page](#)
[Catalog Page - WDK A-30 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Engineering Drawing - DR15 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1579_INSTALLINST](#)
[Literature - Connexion 2.0 Zone Distribution System](#)
[Literature - Hubbell Marine Full Line Catalog](#)
[Sales Drawings - WDK_DR15_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Marine Electrical Products](#)

Series Commercial Specification
Grade
Style Style Line Decorator
Type • Standard Duplex
• Standard Duplex
UPC 783585127781



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-DR15-SPEC-EN | REV 1/2024