

Straight Blade Devices,  
Receptacles, Duplex,  
Decorator/Commercial/Industrial  
Grade, 2-Pole 3-Wire Grounding,  
20A 125V, 5-20R, Brown, Single  
Pack

By Hubbell Wiring Device-Kellems  
Catalog # [DR20](#)

Straight Blade Devices, Receptacles, Duplex,  
Decorator/Commercial/Industrial Grade, 2-Pole 3-Wire  
Grounding, 20A 125V, 5-20R, Brown, Single Pack.

Features

- Aesthetic Style Line® decorator design
- Smooth face
- Triple wipe contacts

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	DR20
EU RoHS Indicator	Yes
Horsepower - Maximum	1
Item Type	Decorator Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Commercial Specification Grade
Specifications	<ul style="list-style-type: none"><li>• Automatic Self-grounding Staple - Stainless steel</li><li>• Base - Nylon</li><li>• Face - Nylon</li><li>• Ground Contacts - Brass</li></ul>



Style  
UPC

- Mounting Screws - Galvanized Steel
  - Mounting Strap - .040 in. (1) Galvanized steel
  - Power Contacts - .030 in. (.8) Brass
  - Terminal Screws - Plated steel
  - Wire Clamp - .062 in. (1.6) Nickel plated steel
- Style Line Decorator  
783585127866

Dimensions

Dimensions	3.28 in x 1.06 in x 1.29 in
Display Size	Standard Sized Product
Height	1.29 in
Length	3.28 in
Weight	0.15 lb
Width	1.06 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA, C22.2, No. 42</li><li>• Fed. Spec. W-C-596</li><li>• NEMA® WD-6 Compliant</li><li>• UL Listed to UL498 File No. E2186</li></ul>
Nema Rating	5-20R

Logistics

Carton Quantity	10
Pallet Quantity	9000

Product Assets

- Catalog Page - [WDK A-31 Catalog Page](#)
- Catalogs - [WDK Catalog Full 2024](#)
- Engineering Drawing - [DR20 AutoCAD Drawing](#)
- Installation Manuals - [WIRING\\_PD1579\\_INSTALLINST](#)
- Literature - [Connexion 2.0 Zone Distribution System](#)
- Sales Drawings - [WDK\\_DR20\\_DRAWING\\_PDF](#)
- Specifications - [DR20 Specification Sheet](#)
- Specifications - [Wiring DR20 Specification Sheet](#)
- Specifications - [DR20 Specification Sheet French](#)
- Warranty - [Industrial & Commercial Products](#)

