

Pre Wired Kit with 5A Circuit  
Breaker and Aux, DIN Rail Box, Gray

By Hubbell Wiring Device-Kellems  
Catalog # [DRUBKITACCB5](#)



Pre Wired Kit with 5A Circuit Breaker and Aux, DIN Rail Box, Gray.

Features

- It provides utility power to any control cabinet
- Optional auxiliary contacts for feed through capability
- Pre-wired "kits" are available for end-user customization

General

Catalog Number	DRUBKITACCB5
Construction	Molded and Fabricated
EU RoHS Indicator	No
Horsepower - Maximum	0.5
Item Type	Component Parts
Knockouts	None
Material	PVC (polyvinyl chloride)
Material - Mounting Hardware	Vertical Mount, DIN Rail Mount
Number Of Outlets	1-Device
Number Of Poles	2-Pole
Specifications	<ul style="list-style-type: none"><li>• Base - PVC</li><li>• Cover/Faceplate - PVC</li><li>• Plug - PVC</li></ul>
Type	Box Only
UPC	783585108223

Dimensions

Dimensions	5.62 in x 3.31 in x 2.54 in
Display Size	Standard Sized Product
Height	2.54 in
Length	5.62 in
Weight	1 lb
Width	3.31 in

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Cable Entry	Terminals
Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	5-15R

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog Page - WDK I-13 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - DRUBKITACCB5 AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD1826\\_INSTALLINST](#)  
[Literature - PULP & PAPER SOLUTIONS](#)  
[Literature - Pulp & Paper Solutions](#)  
[Sales Drawings - WDK\\_DRUBKIT\\_DRAWING\\_PDF](#)  
[Specifications - DRUBKITACCB5 Specification Sheet](#)  
[Specifications - DRUBKITACCB5 Specification Sheet French](#)  
[Specifications - Wiring DRUBKITACCB5 Specification Sheet](#)  
[Warranty - Industrial & Commercial Products](#)