

Switches and Lighting Control,  
Decorator Switch, Specification  
Grade, Three Way, 15A 120/277V  
AC, Back and Side Wired, White

By Hubbell Wiring Device-Kellems  
Catalog # [DS315W](#)



Switches and Lighting Control, Decorator Switch, Specification  
Grade, Three Way, 15A 120/277V AC, Back and Side Wired,  
White

Features

- Thread cleaning captive mounting screw
- Steel, zinc plated bridge is corrosion resistant
- Automatic self-grounding staple

Performance

- Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute
- Electrical - Max. Continuous Current - 15A
- Electrical - Max. Working Voltage - 277V AC
- Electrical - Overload - Minimum 4.8 times rated current for 100 cycles
- Electrical - Temperature Rise - 30°C maximum at rated current
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact
- Mechanical - Terminal Accommodations - #14 AWG min. - #10 AWG max. solid and stranded copper wire only

General

Action	SPDT
Catalog Number	DS315W
Color	White
EU RoHS Indicator	Yes
Item Type	Three Way Style Line Decorator Switch
Material	Thermoplastic
Number Of Poles	Single Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	General Purpose
Specifications	<ul style="list-style-type: none"><li>• Contacts - Silver Alloy</li><li>• Contacts - Silver Alloy</li><li>• Ground Screw - Brass (Green)</li><li>• Mounting Bridge - Nickel Plated Steel with Auto Ground Staple</li></ul>

Style  
UPC

- Rocker Material - Thermoplastic
  - Terminal Screws - Brass
- Three Way  
783585108346

Dimensions

Dimensions	3.91 in x 1.41 in x 1.01 in
Height	1.01 in
Length	3.91 in
Weight	0.2 lb
Width	1.41 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC

Conductor Related

Wire Size	#14 AWG to #10 AWG
-----------	--------------------

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
Pallet Quantity	4500

Product Assets

[Catalog Page - WDK D-15](#) [Catalog Page Catalogs - WDK](#) [Catalog Full 2024](#)  
[Installation Manuals - WIRING\\_PD2444\\_INSTALLINST](#)  
[Sales Drawings - WDK\\_DS315\\_DRAWING\\_PDF](#)



A Hubbell brand