

Switches and Lighting Control,
Decorator Switch, Specification
Grade, Three Way, 20A 120/277V
AC, Back and Side Wired, Gray

By Hubbell Wiring Device-Kellems
Catalog # [DS320GY](#)



Decorator Switch, Specification Grade, Three Way, 20A
120/277V AC, Back and Side Wired

Features

- Thread cleaning captive mounting screw
- Steel, zinc plated bridge is corrosion resistant
- Automatic self-grounding staple

Performance

- Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute
- Electrical - Max. Continuous Current - 20A
- Electrical - Max. Working Voltage - 277V AC
- Electrical - Overload - Minimum 4.8 times rated current for 100 cycles
- Electrical - Temperature Rise - 30°C maximum at rated current
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact
- Mechanical - Terminal Accommodations - #14 AWG min. - #10 AWG max. solid and stranded copper wire only

General

Action	SPDT
Catalog Number	DS320GY
EU RoHS Indicator	No
Item Type	Three Way Style Line Decorator Switch
Material	Thermoplastic
Number Of Poles	Single Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	General Purpose
Specifications	<ul style="list-style-type: none">• Contacts - Silver Alloy• Contacts - Silver Alloy• Ground Screw - Brass (Green)• Mounting Bridge - Nickel Plated Steel with Auto Ground Staple• Rocker Material - Thermoplastic

Style	• Terminal Screws - Brass
UPC	Three Way 783585154466
Dimensions	
Dimensions	3.91 in x 1.41 in x 1.01 in
Height	1.01 in
Length	3.91 in
Weight	0.2 lb
Width	1.41 in
Electrical Ratings	
Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC

Conductor Related

Wire Size	#14 AWG to #10 AWG
-----------	--------------------

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
Pallet Quantity	5000

Product Assets

[Catalog Page - WDK D-15 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_PD2444_INSTALLINST](#)
[Sales Drawings - WDK_DS320_DRAWING_PDF](#)
[Specifications - Wiring DS320GY Specification Sheet](#)
[Specifications - DS320GY Specification Sheet](#)
[Specifications - DS320GY Specification Sheet French](#)



A Hubbell brand